



# HID-High Power ballasts for HPL and HPI lamps

## BHL 1000L 202

The HID High-Power ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

### Product data

<b>Operating and Electrical</b>	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
<b>Wiring</b>	
Connector Type	Screw
<b>Approval and Application</b>	
Approval Marks	CE marking CCC certificate
<b>Product Data</b>	
Order product name	BHL 1000L 202

Full product name	BHL 1000L 202
Full product code	871016305800930
Order code	913710104950
Material Nr. (12NC)	913710104950
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163149196
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163058016

# HID-High Power ballasts for HPL and HPI lamps

## Dimensional drawing

Product	D1	C1	A1	A2
BHL 1000L 202	7 mm	102.0 mm	165 mm	123 mm

