



HID-Basic ballasts for HPL and HPI(PLUS) lamps

BHL 125L 200

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.


Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking CCC certificate
Product Data	
Order product name	BHL 125L 200

Full product name	BHL 125L 200
Full product code	871016303168230
Order code	913710105050
Material Nr. (12NC)	913710105050
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163148540
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163032672

HID-Basic ballasts for HPL and HPI(PLUS) lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 125L 200	6.2 mm	51.5 mm	117.0 mm	102.0 mm	57.1 mm

