



# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## BHL 125L 202


The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BHL 125L 202
Input Voltage	230 V	<b>Full product code</b>		871016303169930
Line Frequency	50 Hz	<b>Order code</b>		913710105150
Input Frequency	50 Hz	<b>Material Nr. (12NC)</b>		913710105150
		<b>Numerator - Quantity Per Pack</b>		1
		<b>EAN/UPC - Product/Case</b>		8710163148564
		<b>Numerator - Packs per outer box</b>		6
		<b>EAN/UPC - Case</b>		8710163032689
<b>Approval and Application</b>				
Approval Marks	CE marking			
<b>Product Data</b>				
Order product name	BHL 125L 202			

# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 125L 202	6.2 mm	51.5 mm	117.0 mm	102.0 mm	57.1 mm

