



HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

BSN 70L 300I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Product data

Operating and Electrical		Full product name	
Input Voltage	220 V	BSN 70L 300I TS	
Line Frequency	50 Hz	Full product code	
Input Frequency	50 Hz	697480505085700	
Wiring		Order code	
Connector Type	Screw	913710106942	
Approval and Application		Material Nr. (12NC)	
Approval Marks	CE marking CCC certificate	913710106942	
Product Data		Numerator - Quantity Per Pack	
Order product name	BSN 70L 300I TS	1	
		EAN/UPC - Product/Case	
		6974805050857	
		Numerator - Packs per outer box	
		6	
		EAN/UPC - Case	
		6974805050864	

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 70L 300I TS	6.2 mm	51.5 mm	117.0 mm	110 mm	57.1 mm

