



# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## BHL 80L 200

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

### Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	BHL 80L 200

Full product name	BHL 80L 200
Full product code	871016306848030
Order code	913710108450
Material Nr. (12NC)	913710108450
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163068480
Numerator - Packs per outer box	6
EAN/UPC - Case	8710163068497

# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 80L 200	6.2 mm	51.5 mm	117.0 mm	102.0 mm	57.1 mm

