



# BTA EM ballasts for TL Fluorescent lamps

## BTA 36W 230V C DI

This efficient, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps features a balanced combination of essential characteristics, thus allowing a wide variety of standard applications.


### Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Double Insert
Mechanical and Housing	
Housing	L 155x39x28
Approval and Application	
Energy Efficiency Index	C
Approval Marks	CE marking

Product Data	
Full product code	871016303374730
Order product name	BTA 36W 230V C DI
Order code	913710112250
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	32
Material Nr. (12NC)	913710112250
Full product name	BTA 36W 230V C DI
EAN/UPC - Case	8710163033754
EAN/UPC - Product/Case	8710163148687

# BTA EM ballasts for TL Fluorescent lamps

## Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BTA 36W	4.0	28.0	1.2	155.0	140.0	48.0	56.0	39.0	20.0
230V C DI	mm	mm	mm	mm	mm	mm	mm	mm	mm

