



# BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

## BPL 18W 230V B2 DI

This standard, reliable, long-life electromagnetic ballast for compact fluorescent lamps provides excellent performance with 2-pin and 4-pin CFLni lamps.


### Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Double Insert
Mechanical and Housing	
Housing	L 85x39x28
Approval and Application	
Energy Efficiency Index	B2
Approval Marks	CE marking

Product Data	
Full product code	871016306586130
Order product name	BPL 18W 230V B2 DI
Order code	913710121450
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48
Material Nr. (12NC)	913710121450
Full product name	BPL 18W 230V B2 DI
EAN/UPC - Case	8710163065878
EAN/UPC - Product/Case	8710163150093

# BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

## Dimensional drawing



Product	D1	C1	A1	A2	A3	A4	B1
BPL 18W 230V	4.0 mm	28.0 mm	110.0 mm	95.0 mm	45.0 mm	33.5 mm	39.0 mm
B2 DI							

