

BTA EM ballasts for TL Fluorescent lamps

BTA 58W 240V B2 'SC

This efficient, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps features a balanced combination of essential characteristics, thus allowing a wide variety of standard applications.


Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Mechanical and Housing	
Housing	L 195x39x28
Approval and Application	
Energy Efficiency Index	B2
Approval Marks	CE marking

Product Data	
Order product name	BTA 58W 240V B2 SC
Full product name	BTA 58W 240V B2 'SC
Full product code	871016308605730
Order code	08605730
Material Nr. (12NC)	913710124150
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163150666
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163069333

BTA EM ballasts for TL Fluorescent lamps

Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BTA 58W	4.0	28.0	1.2	195.0	180.0	48.0	110.0	39.0	20.0
240V B2 SC	mm	mm	mm	mm	mm	mm	mm	mm	mm

