



Mark 10 Powerline

MARK 10 POWERLINE ELE DIM BALLAST (1) 40W CFL (4-PIN) 277V

For companies looking to make their fixed-output linear T8, 4-pin CFL, and T5/HO fluorescent systems more cost effective and sustainable, Mark 10 Powerline ballasts provide an easy solution without the need for additional control leads. Simply, (1) replace the ballast, (2) replace the switch, (3) dim the lights, that is all it takes. It's that easy to bring the convenience and flexibility of fluorescent dimming to conference rooms, private offices, auditoriums, architectural cove lighting – anywhere dimming is required.

Product data


General Information		Input Power (Max)		41 W
Lamp Type	FT40W/2G11	Input Power (Min)		10 W
Number of Lamps	1 piece/unit	Rated Lamp Power		40 W
Ballast Type	Dimmable Fluorescent	Wiring		
Base Model	VEZ1TTS40SC	Color Input Terminals		No terminals
Suitable For Outdoor Use	Yes	Color Output Terminals		No terminals
Automatic Restart	Yes	Wire Striplength		0.50/0.375 mm
Operating and Electrical		Control Wire Gauge		NA
Input Voltage	277 V	Lamp Connection		Series
Input Frequency	60 Hz	Wire Length by Color		See data sheet
Total Harmonic Distortion USA	10 %	Wire Gauge (Nom)		18AWG mm
Ignition Method	Programmed Start	Wire Type		Solid
Crestfactor (Nom)	1.7	Remote Wiring Configuration Allowed		Yes
Ignition Time (Nom)	1.5 s	Tandem Wiring Configuration Allowed		No
Ballast Factor (Max)	1	Through Wiring Configuration Allowed		No
Ballast Factor (Min)	0.05	Max Ballast-Lamp Distance Remote Wiring		6'
Power Factor (Nom)	0.99	Max Ballast-Lamp Distance Tandem Wiring		NA
Input Current (Nom)	0.15 A	Max Ballast-Lamp Distance Through Wiring		NA

Mark 10 Powerline

Connector Type	No connector
Temperature	
T-Case Maximum (Nom)	70 °C
Mechanical and Housing	
Housing Material	Metal
Housing	SC
Housing Dimensions	9.5" x 1.7" x 1.18"
Approval and Application	
EMC Immunity Standard	FCC Consumer
Approval Marks	CSA certificate UL certificate CEC Listing RoHS Compliant

Hum And Noise Level	A
UL Recognized	No
Product Data	
Order product name	MARK 10 POWERLINE ELE DIM BALLAST (1) 40W CFL (4-PIN) 277V
EAN/UPC - Product	781087117033
Order code	913710250602
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	913710250602
Net Weight (Piece)	377.000 g

Dimensional drawing



ELE DIM BALLAST (1) 40W CFL (4-PIN) 277V

Product	A1	A2	B1	C1
MARK 10 POWERLINE VEZITTS40SC35M	9.5 in	8.90 in	1.7 in	1.18 in

