

PHILIPS

Lighting



e-Vision Low Wattage 20-150W

E-VISION ELE MH BAL 70W M139/M143 120-277 50/60HZ

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

Product data

General Information	
ANSI Code	C98-M98,C139-M139,M1
Lamp Type	70W MH
Number of Lamps	1 piece/unit
Ballast Type	Electronic HID
Base Model	IMH70GBLS
Suitable For Outdoor Use	Yes
Operating and Electrical	
Input Voltage	120 to 277 V
Input Frequency	50 to 60 Hz
Total Harmonic Distortion USA	15 %
Crestfactor (Nom)	1.8
Ignition Time (Nom)	1200 s
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Input Current (Max)	0.66 A
Input Current (Min)	0.28 A


Input Power (Nom)	79-76 W
Rated Lamp Power	70 W
Wiring	
Color Input Terminals	No terminals
Color Output Terminals	No terminals
Wire Striplength	0.50 mm
Control Wire Gauge	NA
Wire Length by Color	All leads = 11"
Wire Gauge (Nom)	18AWG mm
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	No
Connector Type	No connector

e-Vision Low Wattage 20-150W

Temperature	
T-Case Maximum (Nom)	90 °C
Mechanical and Housing	
Housing Material	Metal
Housing	G
Housing Dimensions	3.5" x 3.0" x 1.2"
Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approval Marks	CSA certificate UL certificate NOM certificate RoHS Compliant
Hum And Noise Level	A

UL Recognized	No
Product Data	
Order product name	E-VISION ELE MH BAL 70W M139/M143 120-277 50/60HZ
EAN/UPC - Product	781087041864
Order code	913710259702
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	913710259702
Net Weight (Piece)	0.413 kg

Dimensional drawing



E-VISION IMH70GBLSM

Product	A1	A2	A3	A4	A5	B1	B2	C1
E-VISION ELE MH BAL 70W M139/M143 120-277 50/60HZ	3.8 in	3.5 in	3.4 in	2.0 in	1.13 in	3.0 in	2.6 in	1.2 in

