

e-Vision Low Wattage 20-150W

E-VISION ELE MH BAL 2X39W M130 120-277V 50/60HZ

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

Product data


General Information		Input Power (Nom)	
ANSI Code	C130-M130	Rated Lamp Watts	39 W
Lamp Type	39W MH	Wiring	
Number of Lamps	2 piece/unit	Color Input Terminals	No terminals
Ballast Type	Electronic HID	Color Output Terminals	No terminals
Base Model	IMH239ABLS	Wire Striplength	0.50 mm
Suitable For Outdoor Use	Yes	Control Wire Gauge	NA
Operating and Electrical		Wire Length by Color	All leads = 11"
Input Voltage	120 to 277 V	Wire Gauge (Nom)	18AWG mm
Input Frequency	50 to 60 Hz	Wire Type	Stranded
Max THD	15 %	Remote Wiring Configuration Allowed	Yes
Lamp Current Crest Factor (Nom)	1.8	Tandem Wiring Configuration Allowed	No
Ignition Time (Nom)	1200 s	Through Wiring Configuration Allowed	No
Ballast Factor (Nom)	1	Connector Type	No connector
Power Factor (Nom)	0.90		
Input Current (Operating) (Max)	0.74 A		
Input Current (Operating) (Min)	0.31 A		

e-Vision Low Wattage 20-150W

Temperature	
T-Case Maximum (Nom)	85 °C
Mechanical and Housing	
Housing Material	Metal
Housing	A-B
Housing Dimensions	4.7" x 3.6" x 1.5"
Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approbation Marks	CSA certificate UL certificate NOM certificate RoHS Compliant
Sound Rating	A

UL Recognized	No
Product Data	
Order product name	E-VISION ELE MH BAL 2X39W M130 120-277V 50/60HZ
EAN/UPC - Product	781087049280
Order code	IMH239ABL5M
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	913710285402
Net Weight (Piece)	667.000 g

Dimensional drawing



Product	A1	A2	A3	A4	B1	B2	C1
E-VISION ELE MH BAL 2X39W M130 120-277V 50/60HZ	5.5 in	4.7 in	5.2 in	2.0 in	3.6 in	2.9 in	1.5 in

E-VISION IMH239ABL5M

