



# F-can (72C)

## F-CAN HID MH BAL 250W M58 120/277V FCAN

The Philips Advance line of F-can HID ballasts comes in two dual-voltage configurations for the US and Canadian market. Ballasts for these luminaires are most often encased and potted in fluorescent ballast type cans.

#### **Product data**

General Information	
ANSI Code	M58
Lamp Type	250W MH
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	72C5782
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	NA
Capacitor Catalog Number	Inside Can
Automatic Restart	No
Operating and Electrical	
Input Voltage	120/277 V
Input Frequency	60 Hz
Inp. Current (Open Circuit)	2.1/0.9 A
Input Current (Starting)	2.1/0.9 A
Input Current (Short Circuit)	1.7-2.55/0.75-1.1 A
Secondary Short Circuit Current	2.15-2.65 A
Constant Wattage Deviation	10%
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Nominal Open Circuit Voltage	300 V
Input Current (Operating) (Nom)	2.6/1.12 A A
	· · · · · · · · · · · · · · · · · · ·

Input Power (Nom)	290 W
Rated Lamp Watts	250 W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	Determined by AWG used
Recommended Fuse Value	8/4 A
Mechanical and Housing	
Housing Material	Metal
Housing	F-Can
Housing Dimensions	16.7 x 2.63 x 3.19
Approval and Application	
Open Circuit Voltage Test (Volts)	270-330 V
Approbation Marks	CSA certificate UL certificate RoHS
	Compliant
Temperature Marking	90°C max. case
UL Recognized	No
Hipot Test (1 Minute)	1600 V
Hipot Test (2 Seconds)	2000 V


Datasheet, 2019, March 22 data subject to change

## F-can (72C)

UL Insulation Class	A(105°C)
UL Temperature Code	NA
Product Data	
Order product name	F-CAN HID MH BAL 250W M58 120/277V
	FCAN
EAN/UPC - Product	781087025314

Order code	72C5782NP001
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710408901
Net Weight (Piece)	7.036 kg

### Dimensional drawing



MH BAL 250W M58 120/277V FCAN

Product	A1	A2	А3	B1	B2	C1	D1
F-CAN HID MH BAL 250W M58	12 in	16.13 in	15.5 in	3.9 in	2.0 in	2.6 in	0.3 in
120/277V FCAN							

