



# Val-U-Pak Plus (77L)

## CORE & COIL HID HPS BAL 1000W S52 5-TAP KIT WITH LAMP

Our VAL-U-PAK Plus magnetic HID replacement kits assemble the required components — including lamp, core and coil, the appropriate capacitor, ignitor (where required), mounting bracket and hardware, and instructions — in one convenient package. This saves valuable time for MRO and contractor applications.

### Product data

General Information		Operating and Electrical	
ANSI Code	S52	Input Voltage	120/208/240/277/480 V
Lamp Type	1000W HPS	Input Frequency	60 Hz
Number of Lamps	1 piece/unit	Input Current (Open Circuit)	3.9/2.19/2.01/1.71/0.96 A
Circuit Type	CWA	Input Current (Starting)	7.8/4.38/3.82/3.3/1.9 A
Ballast Type	Magnetic HID	Input Current (Short Circuit)	5.83-8.74/3.36-5.05/2.92-4.38/2.53-3.8/1.46-2.19 A
Base Model	77L8753	Secondary Short Circuit	6.24-7.63 A
Core Size	4 1/4 x 6	Current	
Suitable For Outdoor Use	Yes	Constant Wattage Deviation	Within Trapezoid
Ignitor Catalog Number	LI571-H5	Ballast Factor (Nom)	1
Ignitor Temperature Rating	105°C	Power Factor (Nom)	0.90
Capacitor Value	26 MFD	Open Circuit Voltage	437 V
Capacitor Catalog Number	RW1626020	Input Current (Nom)	9.28/5.32/4.68/4.03/2.31 A A
Capacitor Requirements	525V	Input Power (Nom)	1100 W
Capacitor Temperature	90°C	Rated Lamp Power	1000 W
Rating			
Capacitor Diameter/Oval	1.75 in	Wiring	
Dimensions		Wire Striplength	0.5 mm
Capacitor Height	4.25 in	Wire Length by Color	12"
Automatic Restart	No	Wire Type	Stranded
		Remote Wiring	Yes
		Configuration Allowed	

## Val-U-Pak Plus (77L)

Max Ballast-Lamp Distance	15'
Remote Wiring	
Recommended Fuse Value	25/15/12/10/6 A


### Approval and Application

Open Circuit Voltage Test (Volts)	390-476 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C/C/C/C/C
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029C

### Product Data

Order product name	CORE & COIL HID HPS BAL 1000W S52 5-TAP KIT WITH LAMP
EAN/UPC - Product	781087114223
Order code	913710411101
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710411101
Net Weight (Piece)	15.418 kg

### Dimensional drawing



HPS BAL 1000W S52 5-TAP KIT WITH LAMP

Product	C1	C2	A1	A2	A3	B1	B2
CORE & COIL HID 77L8753001	6 in	3.97 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in

