

Core & Coil (71A) MH ~LT~ 175W

CORE & COIL HID MH BAL 70W M98/143 QUAD C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

| General Information | |
|------------------------------|--------------|
| ANSI Code | M98-M143 |
| Lamp Type | 70W MH |
| Number of Lamps | 1 piece/unit |
| Circuit Type | HX-HPF |
| Ballast Type | Magnetic HID |
| Base Model | 71A5292 |
| Core Size | 3 X 4 (2 LW) |
| Suitable For Outdoor Use | Yes |
| Ignitor Catalog Number | LI533-H4 |
| Ignitor Temperature Rating | 105°C |
| Capacitor Value | 8 MFD |
| Capacitor Catalog Number | 7C080L30RA |
| Capacitor Requirements | 280V |
| Capacitor Temperature Rating | 105°C |
| Capacitor Diameter/Oval | 1.25 in |
| Dimensions | |
| Capacitor Height | 2.75 in |
| Automatic Restart | No |


| Operating and Electrical | |
|---------------------------------|---|
| Input Voltage | 120/208/240/277 V |
| Input Frequency | 60 Hz |
| Inp. Current (Open Circuit) | 1.66/0.97/0.83/0.73 A |
| Input Current (Starting) | 0.71/0.41/0.4/0.3 A |
| Input Current (Short Circuit) | 0.65-0.98/0.4-0.6/0.32-0.49/0.29-0.44 A |
| Secondary Short Circuit Current | 1.03-1.26 A |
| Constant Wattage Deviation | 7% |
| Ballast Factor (Nom) | 1 |
| Power Factor (Nom) | 0.90 |
| Nominal Open Circuit Voltage | 255 V |
| Input Current (Operating) (Nom) | 0.85/0.49/0.42/0.37 A A |
| Input Power (Nom) | 92 W |
| Rated Lamp Watts | 70 W |
| Wiring | |
| Wire Striplength | 0.5 mm |
| Wire Length by Color | 12" |
| Wire Type | Stranded |

Core & Coil (71A) MH ~LT~ 175W

| | |
|-------------------------------------|------------------------------------|
| Remote Wiring Configuration Allowed | Yes |
| Max Ballast-Lamp Distance | 15' |
| Remote Wiring | |
| Recommended Fuse Value | 4/3/2/2 A |
| Approval and Application | |
| Open Circuit Voltage Test (Volts) | 230-280 V |
| Approbation Marks | ULR CSA certificate RoHS Compliant |
| Temperature Marking | A/A/A/A |
| UL Recognized | Yes |
| Hipot Test (1 Minute) | 2000 V |
| Hipot Test (2 Seconds) | 2500 V |

| | |
|---------------------------------|---|
| UL Insulation Class | H(180°C) |
| UL Temperature Code | 1029A |
| Product Data | |
| Order product name | CORE & COIL HID MH BAL 70W M98/143 QUAD C&C |
| EAN/UPC - Product | 781087017319 |
| Order code | 71A5292600 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 6 |
| Material Nr. (12NC) | 913710431402 |
| Net Weight (Piece) | 2.210 kg |

Dimensional drawing



MH BAL 70W M98/143 QUAD C&C

| Product | C1 | C2 | A1 | A2 | B1 | B2 |
|----------------------------|---------|---------|--------|--------|--------|--------|
| CORE & COIL HID 71A5292600 | 2.88 in | 1.44 in | 3.9 in | 3.5 in | 2.8 in | 2.4 in |

