



Core & Coil (71A) MH ~LT~ 175W

CORE & COIL HID MH BAL 150W M102/142 480V/120T C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information					
ANSI Code	M102-M142				
Lamp Type	150 MH				
Number of Lamps	1 piece/unit				
Circuit Type	HX-HPF				
Ballast Type	Magnetic HID				
Base Model	71A5442T				
Core Size	3 X 4 (2 coil)				
Suitable For Outdoor Use	Yes				
Ignitor Catalog Number	LI533-H4				
Ignitor Temperature Rating	105°C				
Capacitor Value	16 MFD				
Capacitor Catalog Number	7C160M30RA				
Capacitor Requirements	280V				
Capacitor Temperature Rating	105°C				
Capacitor Diameter/Oval Dimensions	1.65 in				
Capacitor Height	2.75 in				
Automatic Restart	No				

Operating and Electrical				
Input Voltage	480 V			
Input Frequency	60 Hz			
Input Current (Open Circuit)	0.81 A			
Input Current (Starting)	0.45 A			
Input Current (Short Circuit)	0.33-0.49 A			
Secondary Short Circuit Current	1.91-2.33 A			
Constant Wattage Deviation	10%			
Ballast Factor (Nom)	1			
Power Factor (Nom)	0.90			
Open Circuit Voltage	270 V			
Input Current (Nom)	0.42 A A			
Input Power (Nom)	185 W			
Rated Lamp Power	150 W			
Wiring				
Wire Striplength	0.5 mm			
Wire Length by Color	12"			
Wire Type	Stranded			
Remote Wiring Configuration Allowed	Yes			


Datasheet, 2019, March 22 data subject to change

Core & Coil (71A) MH ~LT~ 175W

Max Ballast-Lamp Distance Remote Wiring 10'				
Recommended Fuse Value	3 A			
Approval and Application				
Open Circuit Voltage Test (Volts)	243-297 V			
Approval Marks	ULR CSA certificate RoHS Compliant			
Temperature Marking	В			
UL Recognized	Yes			
Hipot Test (1 Minute)	2000 V			
Hipot Test (2 Seconds)	2500 V			
UL Insulation Class	H(180°C)			
UL Temperature Code	1029B			

Product Data	
Order product name	CORE & COIL HID MH BAL 150W M102/142
	480V/120T C&C
EAN/UPC - Product	781087026335
Order code	913710491402
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	913710491402
Net Weight (Piece)	4.078 kg

Dimensional drawing



MH BAL 150W M102/142 480V/120T C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 150W	3.92 in	2.8 in	3.9 in	3.5 in	2.8 in	2.4 in
M102/142 480V/120T C&C						

