



# Lighting




## Core & Coil (71A) MH ~GT~ 450W

Max Ballast-Lamp Distance Remote Wiring Determined by AWG used	
Recommended Fuse Value	10 A
<b>Approval and Application</b>	
Open Circuit Voltage Test (Volts)	405-495 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	E
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029E

<b>Product Data</b>	
Order product name	CORE & COIL HID MH BAL 1500W M48 480V/120T C&C
EAN/UPC - Product	781087023013
Order code	71A6742600T
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	913710521102
Net Weight (Piece)	13.808 kg

### Dimensional drawing



Product	C1	C2	A1	A2	A3	B1	B2
CORE & COIL HID 71A6742600T	6.2 in	4.2 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in

MH BAL 1500W M48 480V/120T C&C

