



# Transformers

## AUTO-TRANSFORMER ISOXFMR 120:11.5V 75W C&C

Stepdown transformers and autotransformers are used when you need to connect a lower voltage device to a higher voltage source.


### Product data

General Information	
Circuit Type	Transformer
Ballast Type	Magnetic HID
Base Model	71A9743C
Core Size	7/8" E/I
Suitable For Outdoor Use	Yes
Operating and Electrical	
Input Voltage	120:12 V
Input Frequency	60 Hz
Input Current (Operating) (Nom)	0.85 A
Rated Lamp Watts	75 W load W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	6"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Mechanical and Housing	
Housing	NA

Housing Dimensions	NA
Approval and Application	
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	NA
UL Recognized	Yes
UL Insulation Class	H(180°C)
UL Temperature Code	NA
Product Data	
Order product name	AUTO-TRANSFORMER ISOXFMR 120:11.5V 75W C&C
EAN/UPC - Product	781087092767
Order code	71A9743600C
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913710559902
Net Weight (Piece)	1.438 kg

Transformers

Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
AUTO-TRANSFORMER ISOXFMR 120:11.5V 75W C&C	2.8 in	1.5 in	2.6 in	2.2 in	2.2 in	1.8 in

AUTO-TRANSFORMER 71A9743600C

