



Transformers

AUTO-TRANSFORMER ISOXFMR 277:11.8V 75W C&C

Stepdown transformers and autotransformers are used when you need to connect a lower voltage device to a higher voltage source.


Product data

General Information	
Circuit Type	Transformer
Ballast Type	Magnetic HID
Base Model	71A9833C
Core Size	7/8" E/I
Suitable For Outdoor Use	Yes
Operating and Electrical	
Input Voltage	277:12 V
Input Frequency	60 Hz
Input Current (Operating) (Nom)	0.3 A
Rated Lamp Watts	50W/75W load W
Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	6"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Mechanical and Housing	
Housing	NA

Housing Dimensions	NA
Approval and Application	
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	NA
UL Recognized	Yes
UL Insulation Class	H(180°C)
UL Temperature Code	NA
Product Data	
Order product name	AUTO-TRANSFORMER ISOXFMR 277:11.8V 75W C&C
EAN/UPC - Product	781087092774
Order code	71A9833600C
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	16
Material Nr. (12NC)	913710560102
Net Weight (Piece)	1.030 kg

Transformers

Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
AUTO-TRANSFORMER 71A9833600C	2.8 in	1.2 in	2.6 in	2.2 in	2.2 in	1.8 in

AUTO-TRANSFORMER 71A9833600C

