



Core & Coil (71A) MH ~GT~ 450W

CORE & COIL HID MH BAL 1000W M141 QUAD C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data


General Information		Operating and Electrical	
ANSI Code	M141	Input Voltage	120/208/240/277 V
Lamp Type	1000W MH	Input Frequency	60 Hz
Number of Lamps	1 piece/unit	Input Current (Open Circuit)	5/2.7/2.5/2.2 A
Circuit Type	CWA	Input Current (Starting)	7/4/3.5/3 A
Ballast Type	Magnetic HID	Input Current (Short Circuit)	5.3-8/3.1-4.7/2.65-4/2.3-3.5 V
Base Model	71A6591	Secondary Short Circuit Current	4.9-6.1 A
Core Size	4 1/4 x 4 3/4 (2 coil)	Constant Wattage Deviation	10%
Suitable For Outdoor Use	Yes	Ballast Factor (Nom)	1
Ignitor Catalog Number	LI572-H5	Power Factor (Nom)	0.90
Ignitor Temperature Rating	105°C	Open Circuit Voltage	415 V
Capacitor Value	24 MFD	Input Current (Nom)	9/5.2/4.5/3.9 A A
Capacitor Catalog Number	MD2409000	Input Power (Nom)	1070 W
Capacitor Requirements	480V	Rated Lamp Power	1000 W
Capacitor Temperature Rating	90°C		
Capacitor Diameter/Oval Dimensions	1.75 in	Wiring	
Capacitor Height	3.9 in	Wire Striplength	0.5 mm
Automatic Restart	No	Wire Length by Color	12"
		Wire Type	Stranded
		Remote Wiring Configuration Allowed	Yes

Core & Coil (71A) MH ~GT~ 450W

Max Ballast-Lamp Distance Remote	5'
Wiring	
Recommended Fuse Value	20/15/10/10 A
Approval and Application	
Open Circuit Voltage Test (Volts)	370-460 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A/A/A/A
UL Recognized	Yes
Hipot Test (1 Minute)	1500 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	N(AC200°C)
UL Temperature Code	1029A

Product Data	
Order product name	CORE & COIL HID MH BAL 1000W M141 QUAD C&C
EAN/UPC - Product	781087044186
Order code	913710582402
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	913710582402
Net Weight (Piece)	8.605 kg

Dimensional drawing



MH BAL 1000W M141 QUAD C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A6591600	5.25 in	3.32 in	4.8 in	4.4 in	4.3 in	3.9 in

