



Core & Coil (71A) HPS ~LT~ 200W

CORE & COIL HID HPS BAL 35W S76 120V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	S76
Lamp Type	35W HPS
Number of Lamps	1 piece/unit
Circuit Type	R-HPF
Ballast Type	Magnetic HID
Base Model	71A7707B
Core Size	2 5/8 x 2 3/16
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	INTEGRAL
Ignitor Temperature Rating	125°C
Capacitor Value	14 MFD
Capacitor Catalog Number	7C140L12RA
Capacitor Requirements	120V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.25 in
Capacitor Height	2.25 in
Automatic Restart	No
Operating and Electrical	
Input Voltage	120 V

Input Frequency	60 Hz
Inp. Current (Open Circuit)	0.65 A
Input Current (Starting)	0.78 A
Input Current (Short Circuit)	0.45-0.65 A
Secondary Short Circuit Current	0.9-1.4 A
Constant Wattage Deviation	Within Trapezoid
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Nominal Open Circuit Voltage	120 V
Input Current (Operating) (Nom)	0.38 A A
Input Power (Nom)	46 W
Rated Lamp Watts	35 W

Wiring	
Wire Striplength	0.5 mm
Wire Length by Color	12"
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	2'
Recommended Fuse Value	2 A

Core & Coil (71A) HPS ~LT~ 200W

Approval and Application


Open Circuit Voltage Test (Volts)	114-126 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	A
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029A

Product Data

Order product name	CORE & COIL HID HPS BAL 35W S76 120V KIT
--------------------	---

EAN/UPC - Product	781087026328
Order code	71A7707001DB
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710594602
Net Weight (Piece)	758.000 g

Dimensional drawing



HPS BAL 35W S76 120V KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 35W S76 120V KIT	2.2 in	0.65 in	2.6 in	2.2 in	2.2 in	1.8 in

