



Encapsulated Core & Coil (73B)

ENCAPSULATED CORE & COIL HID 73B6092500DAEE

Where quiet performance is required, the standard open core and coil ballast is encapsulated (potted) in a cube-shaped steel can utilizing Class H (180°C) polyester compound.

Product data


General Information			
ANSI Code	M135-M155	Input Frequency	60 Hz
Lamp Type	400W MH	Input Current (Open Circuit)	2.6/1.56/1.31/1.17 A
Number of Lamps	1 piece/unit	Input Current (Starting)	3/1.75/1.5/1.3 A
Circuit Type	SUPER-CWA	Input Current (Short Circuit)	2.4-3.6/1.4-2.1/1.2-1.8/1.05-1.55 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	3.6-4.4 A
Base Model	73B6092AEE	Constant Wattage Deviation	10%
Suitable For Outdoor Use	Yes	Ballast Factor (Nom)	1
Ignitor Catalog Number	LI533-H4	Power Factor (Nom)	0.90
Ignitor Temperature Rating	105°C	Open Circuit Voltage	270 V
Capacitor Value	26 MFD	Input Current (Nom)	3.8/2.2/1.9/1.65 A A
Capacitor Catalog Number	7C260P40R	Input Power (Nom)	454 W
Capacitor Requirements	330V	Rated Lamp Power	400 W
Capacitor Temperature Rating	105°C	Wiring	
Capacitor Diameter/Oval Dimensions	1.75 in	Wire Striplength	0.5 mm
Capacitor Height	4.79999999 in	Wire Length by Color	12"
Automatic Restart	No	Wire Type	Stranded
Operating and Electrical		Remote Wiring Configuration Allowed	Yes
Input Voltage	120/208/240/277 V	Max Ballast-Lamp Distance Remote	2'
		Wiring	

Encapsulated Core & Coil (73B)

Recommended Fuse Value	10/7/5/5 A
Mechanical and Housing	
Housing Material	Metal
Housing	Encap
Housing Dimensions	5.4" x 5.0" x 4.3"
Approval and Application	
Open Circuit Voltage Test (Volts)	235-290 V
Approval Marks	ULR CSA certificate EISA RoHS Compliant
Temperature Marking	C/D/D/D
Hum And Noise Level	B
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	25000 V

UL Insulation Class	H(180°C)
UL Temperature Code	1029D
Product Data	
Order product name	ENCAPSULATED CORE & COIL HID
	73B6092500DAEE
EAN/UPC - Product	781087077429
Order code	913710694702
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	3
Material Nr. (12NC)	913710694702
Net Weight (Piece)	7.072 kg

Dimensional drawing



MH BAL 400W M135/155 QUAD ENCAP

Product	A1	A2	A3	B1	B2	C1	D1
ENCAPSULATED CORE & COIL HID	6.75 in	6 in	5.4 in	4.3 in	2 in	5 in	0.25 in
73B6092500DAEE							

