



# HID-CertaVision for CDM

## HID-CV 70 /S CDM 220-240V

HID-CertaVision electronic ballast for use with ceramic metal-halide (CDM) lamps


### Product data

| Operating and Electrical                     |                 |
|----------------------------------------------|-----------------|
| Input Voltage                                | 220 to 240 V    |
| Line Frequency                               | 50 to 60 Hz     |
| Input Frequency                              | 50 to 60 Hz     |
| Inrush Current Width                         | 0.33 ms         |
| Inrush Current Peak (Nom)                    | 33.0 A          |
| Number of Products on MCB (16A Type B) (Nom) | 20              |
| Wiring                                       |                 |
| Cable Length From Device to Lamp             | 2 m             |
| Connector Type                               | Push            |
| Temperature                                  |                 |
| Ambient temperature range                    | -20 °C to 50 °C |
| T-Case Lifetime (Nom)                        | 85 °C           |
| T-Case Maximum (Max)                         | 85 °C           |
| Mechanical and Housing                       |                 |
| Housing                                      | /S              |

| Approval and Application        |                           |
|---------------------------------|---------------------------|
| Approval Marks                  | CE marking                |
| Product Data                    |                           |
| Order product name              | HID-CV 70 /S CDM 220-240V |
| Full product name               | HID-CV 70 /S CDM 220-240V |
| Full product code               | 871829118257300           |
| Order code                      | 913712007666              |
| Material Nr. (12NC)             | 913712007666              |
| Numerator - Quantity Per Pack   | 1                         |
| EAN/UPC - Product/Case          | 8718291182573             |
| Numerator - Packs per outer box | 12                        |
| EAN/UPC - Case                  | 8718291182580             |

HID-CertaVision for CDM

Dimensional drawing



| Product                      | C1      | A1       | A2      | B1      | B2      | B3     |
|------------------------------|---------|----------|---------|---------|---------|--------|
| HID-CV 70 /S CDM<br>220-240V | 32.1 mm | 110.0 mm | 98.5 mm | 75.0 mm | 63.7 mm | 4.5 mm |

