



# HID-Basic Gearbox system for MHN/CDM lamps

## GBMHA 35L 300I TS/I


The Gearbox is a driver system combining electromagnetic ballast, ignitor and compensating capacitor.

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		GBMHA 35L 300I TS/I
Input Voltage	220 V	<b>Full product code</b>		872790006465000
Line Frequency	50 Hz	<b>Order code</b>		913713016244
Input Frequency	50 Hz	<b>Material Nr. (12NC)</b>		913713016244
		<b>Numerator - Quantity Per Pack</b>		1
		<b>EAN/UPC - Product/Case</b>		8727900064650
		<b>Numerator - Packs per outer box</b>		8
		<b>EAN/UPC - Case</b>		8727900064919
<b>Wiring</b>				
Connector Type	Screw			
<b>Product Data</b>				
Order product name	GBMHA 35L 300I TS/I			

# HID-Basic Gearbox system for MHN/CDM lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
GBMHA 35L 300I TS/I	4.0 mm	90.0 mm	260 mm	206 mm	120 mm	78.0 mm

