



# HID-Basic Gearbox system for MHN/CDM lamps

## GBMHA 70L 300I TS/I


The Gearbox is a driver system combining electromagnetic ballast, ignitor and compensating capacitor.

### Product data

Operating and Electrical		Full product name		GBMHA 70L 300I TS/I	
Input Voltage	220 V	Full product code		872790006466700	
Line Frequency	50 Hz	Order code		913713016344	
Input Frequency	50 Hz	Material Nr. (12NC)		913713016344	
		Numerator - Quantity Per Pack		1	
Wiring		EAN/UPC - Product/Case		8727900064667	
Connector Type	Screw	Numerator - Packs per outer box		8	
		EAN/UPC - Case		8727900064926	
Product Data					
Order product name	GBMHA 70L 300I TS/I				

# HID-Basic Gearbox system for MHN/CDM lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
GBMHA 70L 300I TS/I	4.0 mm	90.0 mm	260 mm	206 mm	120 mm	78.0 mm

