



# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## BHLE 400L 200 TS

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

### Product data

Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking
Product Data	
Order product name	BHLE 400L 200 TS

Full product name	BHLE 400L 200 TS
Full product code	872790084176300
Order code	913713017350
Material Nr. (12NC)	913713017350
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500997876
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900841763

# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## Dimensional drawing



Product	D1	C1	A1	A2	B1
BHLE 400L 200 TS	6.2 mm	64.5 mm	165.0 mm	144.0 mm	75.5 mm

