



HID-Basic ballasts for HPL and HPI(PLUS) lamps

BHLE 400L 200 TS

The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

Product data

| Operating and Electrical | |
|--------------------------|------------------|
| Input Voltage | 220 V |
| Line Frequency | 50 Hz |
| Input Frequency | 50 Hz |
| Wiring | |
| Connector Type | Screw |
| Approval and Application | |
| Approval Marks | CE marking |
| Product Data | |
| Order product name | BHLE 400L 200 TS |

| | |
|---------------------------------|------------------|
| Full product name | BHLE 400L 200 TS |
| Full product code | 872790084176300 |
| Order code | 913713017350 |
| Material Nr. (12NC) | 913713017350 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500997876 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8727900841763 |

HID-Basic ballasts for HPL and HPI(PLUS) lamps

Dimensional drawing

| Product | D1 | C1 | A1 | A2 | B1 |
|------------------|--------|---------|----------|----------|---------|
| BHLE 400L 200 TS | 6.2 mm | 64.5 mm | 165.0 mm | 144.0 mm | 75.5 mm |

