



# HID-Basic ballasts for HPL and HPI(PLUS) lamps

## BHLE 400L 202


The HID-Basic ballast is an impregnated (HID standard) electromagnetic ballast for HID lamps, for use in combination with an external ignitor.

### Product data

Operating and Electrical		Full product name	BHLE 400L 202
Input Voltage	230 V	Full product code	872790084180000
Line Frequency	50 Hz	Order code	913713017650
Input Frequency	50 Hz	Material Nr. (12NC)	913713017650
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500997913
		Numerator - Packs per outer box	6
		EAN/UPC - Case	8727900841800
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking		
Product Data			
Order product name	BHLE 400L 202		

## HID-Basic ballasts for HPL and HPI(PLUS) lamps

### Dimensional drawing



Product	D1	C1	A1	A2	B1
BHLE 400L 202	6.2 mm	64.5 mm	165.0 mm	144.0 mm	75.5 mm

