



HF-Selectalume II for TL5 lamps

HF-S 3/424 TL5 II 220-240V 50/60Hz

HF-Selectalume II is the most cost-effective, reliable, slim and affordable fluorescent solution, with highly disruptive technology for energy saving, system flexibility and unsurpassed performance. The cost-saving HF-Selectalume II has a robust design which meets all relevant international safety and performance standards. HF-Selectalume II is intended for use with indoor lighting fixtures such as spotlights, downlights and recessed luminaires, which are largely used in office, retail, industry, hotel, restaurant and other applications where control devices are installed with occasional On/Off switching activity

Product data


Operating and Electrical		T-Case Lifetime (Nom)		75 °C
Input Voltage	220 to 240 V	T-Case Maximum (Max)		75 °C
Line Frequency	50 to 60 Hz			
Input Frequency	50 to 60 Hz	Mechanical and Housing		
Earth Leakage Current (Max)	0.5 mA	Housing		L 280x39x21.5
Inrush Current Width	0.35 ms			
Inrush Current Peak (Max)	30 A	Approval and Application		
Number of Products on MCB (16A Type B) (Nom)	15	Ingress protection code	IP20 [Finger-protected]	
		Energy Efficiency Index	A2 BAT	
		Approval Marks	F-Marking CE marking ENEC certificate CCC certificate C-Tick certificate PSB certification TISI marking SIRIM approval CB Certificate CCC certificate VDE-EMV certificate	
		Product Data		
		Order product name	HF-S 3/424 TL5 II 220-240V 50/60Hz	
		Full product name	HF-S 3/424 TL5 II 220-240V 50/60Hz	

HF-Selectalume II for TL5 lamps

Full product code	872790093937800
Order code	913713034666
Material Nr. (12NC)	913713034666
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900939378

Numerator - Packs per outer box	10
EAN/UPC - Case	8727900939385

Dimensional drawing



Product
HF-S 3/424 TL5 II 220-240V 50/60Hz

Product	A1	B1	C1	A2	B2	D1
HF-S 3/424 TL5 II 220-240V 50/60Hz	280 mm	39 mm	21.5 mm	265 mm		4.2 mm

