



EB-Certalume for TL5 lamps

EB-C 314 TL5 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for TL5 fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts


Product data

| Operating and Electrical | |
|---------------------------------|---|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Earth Leakage Current (Max) | 0.7 mA |
| Wiring | |
| Connector Type Input Terminals | 250 manual connector [Suitable for manual wiring and easy release button] |
| Color Input Terminals | Orange |
| Color Output Terminals | Grey |
| Connector Type Output Terminals | 250 manual connector [Suitable for manual wiring and easy release button] |
| Temperature | |
| T-Case Lifetime (Nom) | 75 °C |
| Mechanical and Housing | |
| Housing | L260x40x25.4 |

| Approval and Application | |
|---------------------------------|--------------------------------|
| Ingress protection code | IP20 [Finger-protected] |
| Energy Efficiency Index | A2 |
| Approval Marks | CCC certificate CB Certificate |
| Product Data | |
| Order product name | EB-C 314 TL5 220-240V 50/60Hz |
| Full product name | EB-C 314 TL5 220-240V 50/60Hz |
| Full product code | 872790090299000 |
| Order code | 90299000 |
| Material Nr. (12NC) | 913713196714 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500999207 |
| Numerator - Packs per outer box | 20 |
| EAN/UPC - Case | 8727900902990 |

EB-Certalume for TL5 lamps

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|-------------------------------|--------|---------|----------|----------|---------|
| EB-C 314 TL5 220-240V 50/60Hz | 4.2 mm | 25.4 mm | 260.0 mm | 250.0 mm | 40.0 mm |

