



EB-Certalume for TL5 lamps

EB-C 314 TL5 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for TL5 fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Earth Leakage Current (Max)	0.7 mA
Wiring	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Temperature	
T-Case Lifetime (Nom)	75 °C
Mechanical and Housing	
Housing	L260x40x25.4

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A2
Approval Marks	CCC certificate CB Certificate
Product Data	
Order product name	EB-C 314 TL5 220-240V 50/60Hz
Full product name	EB-C 314 TL5 220-240V 50/60Hz
Full product code	872790090299000
Order code	913713196714
Material Nr. (12NC)	913713196714
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500999207
Numerator - Packs per outer box	20
EAN/UPC - Case	8727900902990

EB-Certalume for TL5 lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 314 TL5 220-240V 50/60Hz	4.2 mm	25.4 mm	260.0 mm	250.0 mm	40.0 mm

