



EB-Certalume for PLT/C lamps

EB-C 126 PL-T/C 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for 4-pin PL-T and PL-C fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts


Product data

| Operating and Electrical | |
|--|---|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Number of Products on MCB (16A Type B) (Nom) | 20 |
| Wiring | |
| Connector Type Input Terminals | 250 manual connector [Suitable for manual wiring and easy release button] |
| Color Input Terminals | Orange |
| Color Output Terminals | Grey |
| Connector Type Output Terminals | 250 manual connector [Suitable for manual wiring and easy release button] |
| Temperature | |
| T-Case Lifetime (Nom) | 65 °C |
| T-Case Maximum (Max) | 65 °C |
| Mechanical and Housing | |
| Housing | - [Not Specified] |

| Approval and Application | |
|---------------------------------|----------------------------------|
| Ingress protection code | IP20 [Finger-protected] |
| Energy Efficiency Index | A2 |
| Approval Marks | CCC certificate CB Certificate |
| Product Data | |
| Order product name | EB-C 126 PL-T/C 220-240V 50/60Hz |
| Full product name | EB-C 126 PL-T/C 220-240V 50/60Hz |
| Full product code | 872790088904800 |
| Order code | 88904800 |
| Material Nr. (12NC) | 913713198814 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500998934 |
| Numerator - Packs per outer box | 24 |
| EAN/UPC - Case | 8727900889048 |

EB-Certalume for PLT/C lamps

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|----------------------------------|--------|---------|---------|---------|---------|
| EB-C 126 PL-T/C 220-240V 50/60Hz | 4.2 mm | 31.0 mm | 94.0 mm | 86.0 mm | 72.0 mm |

