



# EB-Certalume for TL-D lamps

## EB-C 236 TL-D 220-240V 50/60Hz

EB-Certalume is the most cost-effective, slim and affordable ballast for reliable operation of a fluorescent lamp. It is also the ideal entry-level product for electromagnetic system users who want to enjoy the benefits offered by electronic ballasts. The cost-saving and reliable EB-Certalume has energy efficiency class A2, and its robust design meets all relevant international safety and performance standards. EB-Certalume is intended for use with indoor lighting fixtures such as recessed luminaires, which are widely used in office, industrial, hotel, restaurant and other applications.

### Product data


<b>Operating and Electrical</b>		<b>Temperature</b>	
Input Voltage	220 to 240 V	T-Case Lifetime (Nom)	75 °C
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz	<b>Mechanical and Housing</b>	
Number of Products on MCB (16A Type B) (Nom)	28	Housing	L 210x40x30
		<b>Approval and Application</b>	
<b>Wiring</b>		Ingress protection code	IP20 [Finger-protected]
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]	Energy Efficiency Index	A2
Color Input Terminals	Orange	Approval Marks	CCC certificate CB Certificate
Color Output Terminals	Grey		
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]	<b>Product Data</b>	
		Order product name	EB-C 236 TL-D 220-240V 50/60Hz
		Full product name	EB-C 236 TL-D 220-240V 50/60Hz
		Full product code	872790085880800
		Order code	85880800
		Material Nr. (12NC)	913713199315

EB-Certalume for TL-D lamps

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500998163
Numerator - Packs per outer box	20

EAN/UPC - Case	8727900858808
----------------	---------------

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 236 TL-D 220-240V 50/60Hz	4.2 mm	30.0 mm	210.0 mm	200.0 mm	40.0 mm

