

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

BSNE 150L 304I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


Product data

| | |
|---------------------------------|-------------------|
| Operating and Electrical | |
| Input Voltage | 220 V |
| Line Frequency | 50 Hz |
| Input Frequency | 50 Hz |
| Wiring | |
| Connector Type | Screw |
| Approval and Application | |
| Approval Marks | CE marking |
| Product Data | |
| Order product name | BSNE 150L 304I TS |

| | |
|---------------------------------|-------------------|
| Full product name | BSNE 150L 304I TS |
| Full product code | 871829112576100 |
| Order code | 913713202550 |
| Material Nr. (12NC) | 913713202550 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291125761 |
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8718291125778 |

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

Dimensional drawing



| Product | C1 | A1 | B1 |
|-------------------|---------|----------|---------|
| BSNE 150L 304I TS | 64.5 mm | 125.0 mm | 72.5 mm |

