

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

BSNE 400L 301I TS

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.


Product data

| Operating and Electrical | |
|--------------------------|-------------------|
| Input Voltage | 220 V |
| Line Frequency | 50 Hz |
| Input Frequency | 50 Hz |
| Wiring | |
| Connector Type | Screw |
| Approval and Application | |
| Approval Marks | CE marking |
| Product Data | |
| Order product name | BSNE 400L 301I TS |

| | |
|---------------------------------|-------------------|
| Full product name | BSNE 400L 301I TS |
| Full product code | 871829112582200 |
| Order code | 913713202850 |
| Material Nr. (12NC) | 913713202850 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291125822 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 8718291125839 |

HID-Basic Semi-Parallel Economic ballasts for SON/CDM/MH lamps

Dimensional drawing



| Product | C1 | A1 | B1 |
|-------------------|---------|----------|---------|
| BSNE 400L 3011 TS | 82.0 mm | 165.0 mm | 92.0 mm |

