



# MasterColor CDM-TM

## MMC LAMPKIT CDM-TM 20W/830

Introducing the smallest 20W ceramic metal halide lamp together with the unique e-Vision® electronic ballast. It's visually pleasing and financially rewarding, so the focus can be on your merchandise and not the ceiling clutter.

### 安全提示

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

### 产品数据

| 一般信息                |                       |
|---------------------|-----------------------|
| 底盖                  | PGJ5 [PGJ5]           |
| 操作位置                | UNIVERSAL [任意或通用 (U)] |
| 50% 故障条件下的使用寿命 (标称) | 12,000 小时             |
| 灯技术                 |                       |
| 颜色代码                | 830 [CCT of 3000K]    |
| 颜色名称                | 暖白色 (WW)              |
| 色度坐标 X (标称)         | 0.433                 |
| 色度坐标 Y (标称)         | 0.392                 |
| 相关色温 (标称)           | 3000 K                |
| 光效 (额定) (标称)        | 75 lm/W               |
| 显色指数 (CRI)          | 87                    |
| 弧长 O (标称)           | 3 mm                  |
| 操作和电气               |                       |
| 功耗                  | 22.0 W                |


| 电压 (标称)        | 100 V                      |
|----------------|----------------------------|
| 电压 (标称)        | 100 V                      |
| 控制和调光          |                            |
| 可调光            | 否                          |
| 机械和外壳          |                            |
| 灯泡外观           | 透明                         |
| 灯泡外形           | T13.3 [T 13.3 毫米]          |
| 审批和申请          |                            |
| 汞 (Hg) 含量 (标称) | 2.4 mg                     |
| 能耗 kWh/1000 h  | 24 kWh                     |
| 产品数据           |                            |
| 订单产品名称         | MMC LAMPKIT CDM-TM 20W/830 |
| 完整的产品名称        | MMC LAMPKIT CDM-TM 20W/830 |

MasterColor CDM-TM

|                |                 |
|----------------|-----------------|
| 完整产品代码         | 871150020766115 |
| 订购代码           | 914499996230    |
| 材料编号 (12NC)    | 914499996230    |
| 计算器 - 每包数量     | 1               |
| EAN/UPC - 产品/箱 | 8711500207661   |


|                  |               |
|------------------|---------------|
| 计算器 - 每个外包装箱中的包数 | 12            |
| EAN/UPC - 案例     | 8711500207579 |

二维绘图




| Product                    | D (max) | D       | O    | L (min) | L (max) | L       | C (max) |
|----------------------------|---------|---------|------|---------|---------|---------|---------|
| MMC LAMPKIT CDM-TM 20W/830 | 13.3 mm | 0.44 in | 3 mm | 22.3 mm | 22.9 mm | 22.6 mm | 52 mm   |

光度数据




Light Distribution Diagram - MMC LAMPKIT CDM-TM 20W/830



Spectral Power Distribution Colour

寿命



Life Expectancy Diagram - MMC LAMPKIT CDM-TM 20W/830



Lumen Maintenance Diagram - MMC LAMPKIT CDM-TM 20W/830

