



MasterColor CDM-TM

MASTERC CDM-TM MINI 35W/930 PGJ5 SYS/12

Introducing the smallest 20W ceramic metal halide lamp together with the unique e-Vision® electronic ballast. It's visually pleasing and financially rewarding, so the focus can be on your merchandise and not the ceiling clutter.

Wskazówki bezpieczeństwa i ostrzeżenia

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Dane produktu

Informacje ogólne	
Podstawa-nasadka	PGJ5 [PGJ5]
Pozycja robocza	UNIWERSALNE [Dowolne lub Uniwersalne (U)]
Trwałość do przygaśnięcia do 50% (Nom)	12 000 h
Dane techniczne oświetlenia	
Kod barwy	930 [CCT of 3000K]
Oznaczenie koloru	barwa ciepło-biała (WW)
Współrzędna Chromatyczności X (Nom)	0,436
Współrzędna Chromatyczności Y (Nom)	0,396
Skorelowana Temperatura Barwowa (Nom)	3000 K
Skuteczność świetlna (znamionowa) (Nom)	77 lm/W
Wskaźnik oddawania barw (CRI)	91
Długość łuku O (Nom)	4 mm


Eksploatacja i połączenie elektryczne	
Zużycie energii	39,0 W
Napięcie (Nom)	96 V
Napięcie (Nom)	96 V
Układy sterowania i ściemnianie	
Z możliwością przyciemniania	Nie
Mechanika i korpus	
Wykończenie żarówki	Przezroczyste
Kształt bańki	T13.3 [T 13,3 mm]
Certyfikaty i zastosowania	
Zawartość rtęci (Hg) (Nom)	2,74 mg
Zużycie energii elektrycznej w kWh/1000 h	43 kWh

MasterColor CDM-TM

Dane techniczne produktu	
Nazwa produktu na zamówieniu	MASTERC CDM-TM MINI 35W/930 PGJ5 KIT/12
Pełna nazwa produktu	MASTERC CDM-TM MINI 35W/930 PGJ5 SYS/12
Full EOC	871150021292415
Kod zamówienia	21292415


Materiał Nr (12NC)	914499997330
Numerator - Quantity Per Pack	1
EAN/UPC – Produkt/opakowanie	8711500212924
Numerator - Packs per outer box	12
EAN/UPC – Opakowanie	8711500212931

Rysunki techniczne




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TM	13,3 mm	0,44 in	4 mm	22,3 mm	22,9 mm	22,6	52 mm
MINI 35W/930 PGJ5						mm	
KIT/12							

Dane fotometryczne




Light Distribution Diagram - MASTERC CDM-TM MINI 35W/930 PGJ5 KIT/12




Spectral Power Distribution Colour

Okres eksploatacji



Life Expectancy Diagram - MASTERC CDM-TM MINI 35W/930 PGJ5 KIT/12



Lumen Maintenance Diagram

