



Copenhagen

CGS443 PL-T/4P42W/830 HFP FG GR C10K 363

Little Copenhagen, MASTER PL-T 4 Pin, 42 W, HF Performer

Copenhagen was developed in conjunction with Copenhagen's Office of City Architecture to enhance the aesthetic appeal of the city's lighting. The result is a luminaire that can be used for a number of applications, from roads to squares, while maintaining design consistency. Copenhagen is available in two sizes to ensure that the scale of the luminaire is always in keeping with the varying heights of poles and suspensions. A choice of symmetrical or asymmetrical distributions and a wide selection of light sources, including state-of-the-art LED technology, complete the specification of an extremely adaptable luminaire.

Product data

General Information		Cable	
Lamp family code	PL-T/4P [MASTER PL-T 4 Pin]	Cable 10 m without plug	
Gear	HFP [HF Performer]	Mechanical and Housing	
Product family code	CGS443 [Little Copenhagen]	Housing Color	Grey
Embedded control	-	Mounting device	-
CE mark	Yes	Approval and Application	
ENEC mark	ENEC mark	Ingress protection code	IP44 [Wire-protected, splash-proof]
Light Technical		Mech. impact protection code	IK07 [2 J reinforced]
Number of light sources	1	Protection class IEC	Safety class II
Light source color	830 warm white	Product Data	
Optical cover type	Flat glass	Order product name	CGS443 PL-T/4P42W/830 HFP FG GR C10K 363
Optic type outdoor	Asymmetrical	Full product name	CGS443 PL-T/4P42W/830 HFP FG GR C10K 363
Operating and Electrical		Full product code	570159108914000
Input Voltage	220 to 230 V	Order code	919008627261
Power Consumption	42 W	Material Nr. (12NC)	919008627261

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	5701591089140
Numerator - Packs per outer box	1

EAN/UPC - Case	5701591089140
----------------	---------------

Dimensional drawing

