



Copenhagen

CGS443 PL-T/4P42W K HFP GF GR C10K

Little Copenhagen, MASTER PL-T 4 Pin, 42 W, HF Performer, Glass frosted

Copenhagen was developed in conjunction with Copenhagen's Office of City Architecture to enhance the aesthetic appeal of the city's lighting. The result is a luminaire that can be used for a number of applications, from roads to squares, while maintaining design consistency. Copenhagen is available in two sizes to ensure that the scale of the luminaire is always in keeping with the varying heights of poles and suspensions. A choice of symmetrical or asymmetrical distributions and a wide selection of light sources, including state-of-the-art LED technology, complete the specification of an extremely adaptable luminaire.

Product data

General Information		Operating and Electrical	
Lamp family code	PL-T/4P [MASTER PL-T 4 Pin]	Input Voltage	220 to 230 V
Gear	HFP [HF Performer]	Power Consumption	42 W
Product family code	CGS443 [Little Copenhagen]	Cable	Cable 10 m without plug
Embedded control	-	Mechanical and Housing	
CE mark	Yes	Housing Color	Grey
ENEC mark	ENEC mark	Mounting device	-
Light Technical		Approval and Application	
Number of light sources	1	Ingress protection code	IP44 [Wire-protected, splash-proof]
Light source color	830 warm white	Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Glass frosted	Protection class IEC	Safety class II
Optic type outdoor	Asymmetrical		

Product Data	
Order product name	CGS443 PL-T/4P42W K HFP GF GR C10K
Full product name	CGS443 PL-T/4P42W K HFP GF GR C10K
Full product code	570159109193800
Order code	919008627979
Material Nr. (12NC)	919008627979

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	5701591091938
Numerator - Packs per outer box	1
EAN/UPC - Case	5701591091938

Dimensional drawing

