



# ParkView LED

## BPS965 GRN60/840 II GR CLO-DDF6 C4K 60P

Parkview LED, LED GreenLine 6000 lm, Constant light output and DynaDimmer fixed presets version 6, Post-top for diameter 60 mm

For urban settings, customers want a luminaire that combines unobtrusive elegance with operational efficiency. ParkView LED's unique construction of clear polycarbonate and white lamellas gives the luminaire a sense of lightness and minimalism. Its cone-shaped bowl marked in quarters, cone-shaped louver and base ensure a smooth transition to the pole. ParkView LED provides a symmetrical light distribution, and the vertical lamellas which direct the light towards the ground also cut spill light and minimize glare as they shield the light source. Design: Tegnestuen Bjarne Frost, Denmark

### Product data

| General Information                |                                                              | Color rendering index (CRI)     |                          | 83 |
|------------------------------------|--------------------------------------------------------------|---------------------------------|--------------------------|----|
| Lamp family code                   | GRN60 [LED GreenLine 6000 lm]                                | Number of light sources         | 1                        |    |
| Light source replaceable           | Yes                                                          | Light source color              | 840 neutral white        |    |
| Driver included                    | Yes                                                          | <b>Operating and Electrical</b> |                          |    |
| Product family code                | BPS965 [Parkview LED]                                        | Input Voltage                   | 220 to 240 V             |    |
| Lighting Technology                | LED                                                          | Line Frequency                  | 50 to 60 Hz              |    |
| CE mark                            | Yes                                                          | Power Consumption               | 58 W                     |    |
| Embedded control                   | Constant light output and DynaDimmer fixed presets version 6 | Cable                           | Cable 4.0 m without plug |    |
| <b>Light Technical</b>             |                                                              | <b>Temperature</b>              |                          |    |
| Luminous Flux                      | 4,500 lm                                                     | Ambient temperature range       | -30 to +25 °C            |    |
| Correlated Color Temperature (Nom) | 4000 K                                                       |                                 |                          |    |
| Luminous Efficacy (rated) (Nom)    | 78 lm/W                                                      |                                 |                          |    |

## ParkView LED

### Controls and Dimming

|                               |                              |
|-------------------------------|------------------------------|
| Dimmable                      | Yes                          |
| Driver/power unit/transformer | Power supply unit regulating |
| Control interface             | -                            |
| Constant light output         | Yes                          |

### Mechanical and Housing

|                  |                             |
|------------------|-----------------------------|
| Housing Material | Aluminum                    |
| Housing Color    | Grey                        |
| Mounting device  | Post-top for diameter 60 mm |

### Approval and Application

|                              |                                              |
|------------------------------|----------------------------------------------|
| Ingress protection code      | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected]                  |
| Protection class IEC         | Safety class II                              |

### Initial Performance (IEC Compliant)

|                                       |      |
|---------------------------------------|------|
| Init. Color Rendering Index Tolerance | +/-2 |
|---------------------------------------|------|

### Product Data

|                                 |                                         |
|---------------------------------|-----------------------------------------|
| Order product name              | BPS965 GRN60/840 II GR CLO-DDF6 C4K 60P |
| Full product name               | BPS965 GRN60/840 II GR CLO-DDF6 C4K 60P |
| Full product code               | 871829156311200                         |
| Order code                      | 919008630244                            |
| Material Nr. (12NC)             | 919008630244                            |
| Numerator - Quantity Per Pack   | 1                                       |
| EAN/UPC - Product/Case          | 8718291563112                           |
| Numerator - Packs per outer box | 1                                       |
| EAN/UPC - Case                  | 8718291563112                           |

## Dimensional drawing

