



# Copenhagen LED Big

## BDS441 GRN59-3S/740 II O-DC CLO C13K

Big Copenhagen LED central, LED GreenLine 5900 lm, 740 neutral white, Safety class II, Distribution comfort, Constant light output, Cable 13 m without plug

Copenhagen LED was co-designed together with Copenhagen's Office of City Architecture in order to enhance the aesthetic appeal of the city's lighting. The luminaire's timeless design comes in two sizes – mini and large – to ensure that the dimensions of the luminaire and pole are well balanced, and that the installation blends in harmoniously with its surroundings. A variety of suspensions are available, offering maximum freedom in the overall design of the installation. A choice of symmetrical or asymmetrical distributions and state-of-the-art LED technology complete the specification of an extremely adaptable luminaire.

### Product data

General Information		Lighting Technology	
Lamp family code	GRN59 [LED GreenLine 5900 lm]	Lighting Technology	LED
Light source replaceable	Yes	Embedded control	Constant light output
Number of gear units	1 unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	For mounting on normally flammable surfaces
Light source engine type	LED	ENEC mark	-
Product family code	BDS441 [Big Copenhagen LED central]	EU RoHS compliant	Yes
		Light Technical	
		Upward light output ratio	0
		Luminous Flux	4,960 lumen
		Standard tilt angle posttop	0°
		Standard tilt angle side entry	0°

# Copenhagen LED Big

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	106 lm/W
Color rendering index (CRI)	≥70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution comfort

## Operating and Electrical

Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	41 W
Average CLO power consumption	46 W
End CLO power consumption	51 W
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	46 W
Power Factor (Fraction)	0.9
Connection	-
Cable	Cable 13 m without plug
Number of products on MCB of 16 A type B	8

## Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating with constant light output
Control interface	-
Constant light output	Yes

## Mechanical and Housing

Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Opal
Mounting device	-

Optical cover shape	Flat
Optical cover finish	Clear
Overall height	367 mm
Overall diameter	462 mm
Effective projected area	0.13 m <sup>2</sup>

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

## Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

## Product Data

Full product code	871829156176700
Order product name	BDS441 GRN59-3S/740 II O-DC CLO C13K
Order code	919008632136
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	919008632136
Full product name	BDS441 GRN59-3S/740 II O-DC CLO C13K
EAN/UPC - Case	8718291561767
EAN/UPC - Product/Case	8718291561767

## Copenhagen LED Big

