



# Copenhagen LED Small

## BRS443 GRN29-3S/740 II O-DW CLO-DDF6

Little Copenhagen LED side entry, LED GreenLine 2900 lm, 740 neutral white, Safety class II, Distribution wide, Constant light output and DynaDimmer fixed presets version 6

Copenhagen LED was co-designed together with Copenhagen's Office of City Architecture in order to enhance the aesthetic appeal of the city's lighting. The luminaire's timeless design comes in two sizes – mini and large – to ensure that the dimensions of the luminaire and pole are well balanced, and that the installation blends in harmoniously with its surroundings. A variety of suspensions are available, offering maximum freedom in the overall design of the installation. A choice of symmetrical or asymmetrical distributions and state-of-the-art LED technology complete the specification of an extremely adaptable luminaire.

### Product data

General Information			
Lamp family code	GRN29 [LED GreenLine 2900 lm]	extreme ambient temperatures the luminaire might automatically dim down to protect components	
Light source replaceable	Yes		
Number of gear units	1 unit	Light source engine type	
Driver included	Yes	LED	
Remarks	* -Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At	Product family code	
		BRS443 [Little Copenhagen LED side entry]	
		Lighting Technology	
		LED	
		Embedded control	
		Constant light output and DynaDimmer fixed presets version 6	
		CE mark	
		Yes	
		Warranty period	
		5 years	
		Flammability mark	
		For mounting on normally flammable surfaces	
		ENEC mark	
		-	

# Copenhagen LED Small

EU RoHS compliant	Yes
<b>Light Technical</b>	
Upward light output ratio	0
Luminous Flux	2,480 lumen
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	89 lm/W
Color rendering index (CRI)	≥70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution wide
<b>Operating and Electrical</b>	
Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	24 W
Average CLO power consumption	27 W
End CLO power consumption	30 W
Inrush current	27 A
Inrush time	0.265 ms
Power Consumption	27 W
Power Factor (Fraction)	0.9
Connection	-
Cable	Cable 10 m without plug
Number of products on MCB of 16 A type B	20
<b>Temperature</b>	
Ambient temperature range	-40 to +50 °C
<b>Controls and Dimming</b>	
Dimmable	No
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	-
Constant light output	Yes
<b>Mechanical and Housing</b>	
Reflector material	-
Optic material	Polycarbonate

Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Opal
Mounting device	Side-entry for diameter 48 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall height	312 mm
Overall diameter	380 mm
Effective projected area	0.08 m²
<b>Approval and Application</b>	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class II
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
<b>Product Data</b>	
Full product code	871829156371600
Order product name	BRS443 GRN29-3S/740 II O-DW CLO-DDF6
Order code	919008632178
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	919008632178
Full product name	BRS443 GRN29-3S/740 II O-DW CLO-DDF6
EAN/UPC - Case	8718291563716
EAN/UPC - Product/Case	8718291563716

Copenhagen LED Small

Dimensional drawing

