



TBS050 A

TBS050 A2XTLD-16W/840 EB C1

2, MASTER TL-D, 16 W, 840 neutral white, Electronic, High-gloss mirror flat lamellae louver

The TBS050 luminaires were specially developed for interior commercial lighting, and are available in recessed (TBS050) and surface-mounted (TCS050) models. This is an economical modular range for use with tubular fluorescent lamps of 16, 20, 32 or 40 W. The TBS can be recessed in any type of ceiling (plaster or paneled) and offers the option of two optical systems that offer design freedom in projects, energy savings, excellent lighting efficiency, and easy installation.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	High-gloss mirror flat lamellae louver
Operating and Electrical	
Power Consumption	16 W

Product Data	
Order product name	TBS050 A2XTLD-16W/840 EB C1
Full product name	TBS050 A2XTLD-16W/840 EB C1
Full product code	919106024579
Order code	919106024579
Material Nr. (12NC)	919106024579
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

TBS050 A

Dimensional drawing

Dimensões em mm:

Embutir (TBS 050)

