



# SlimLine TBS020

## TBS020 2XTL-D32W/840 EB R-H

2, MASTER TL-D, 32 W, 840 neutral white, Electronic, Reflector high reflectance

SlimLine luminaires are compact and versatile for better distribution of light in the environment. Their slim design offers lots of advantages to designers and installers, with better adaptation to ceilings. Available in recessed (TBS020) and surface-mounted (TCS020) models with a choice of four optical systems. Ideal for 16 and 32 W TL-D tubular fluorescent lamps.

### Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	Reflector high reflectance
Optical cover type	-
Operating and Electrical	
Power Consumption	32 W

Product Data	
Order product name	TBS020 2XTL-D32W/840 EB R-H
Full product name	TBS020 2XTL-D32W/840 EB R-H
Full product code	919106026481
Order code	919106026481
Material Nr. (12NC)	919106026481
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# SlimLine TBS020

## Dimensional drawing

Dimensões em mm:

Embutir (TBS 020)

