



# SlimLine TBS020

## TBS020 2xTL-D32W/840 EB AC

2, MASTER TL-D, 32 W, 840 neutral white, Electronic, Acrylic bowl/cover

SlimLine luminaires are compact and versatile for better distribution of light in the environment. Their slim design offers lots of advantages to designers and installers, with better adaptation to ceilings. Available in recessed (TBS020) and surface-mounted (TCS020) models with a choice of four optical systems. Ideal for 16 and 32 W TL-D tubular fluorescent lamps.

### Product data

| General Information      |                    |
|--------------------------|--------------------|
| Lamp family code         | TL-D [MASTER TL-D] |
| Gear                     | EB [Electronic]    |
| Light Technical          |                    |
| Number of light sources  | 2                  |
| Light source color       | 840 neutral white  |
| Optic type               | -                  |
| Optical cover type       | Acrylic bowl/cover |
| Operating and Electrical |                    |
| Power Consumption        | 32 W               |

| Product Data                    |                            |
|---------------------------------|----------------------------|
| Order product name              | TBS020 2xTL-D32W/840 EB AC |
| Full product name               | TBS020 2xTL-D32W/840 EB AC |
| Full product code               | 919106026581               |
| Order code                      | 919106026581               |
| Material Nr. (12NC)             | 919106026581               |
| Numerator - Quantity Per Pack   | 1                          |
| Numerator - Packs per outer box | 1                          |

SlimLine TBS020

Dimensional drawing

Dimensões em mm:

Embutir (TBS 020)

