



# SlimLine TCS020

## TCS020 2xTL-D32W/840 EB AC

2, MASTER TL-D, 32 W, 840 neutral white, Electronic, Acrylic bowl/cover

SlimLine luminaires are compact and versatile to allow better distribution of light in the environment. Their slim design offers lots of advantages to designers and installers, with better adaptation to ceilings. Available in recessed (TBS020) and surface-mounted (TCS020) models with a choice of four optical systems. Ideal for 16 and 32 W TL-D tubular fluorescent lamps.

### Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	-
Optical cover type	Acrylic bowl/cover
Operating and Electrical	
Power Consumption	32 W

Product Data	
Order product name	TCS020 2xTL-D32W/840 EB AC
Full product name	TCS020 2xTL-D32W/840 EB AC
Full product code	919106027271
Order code	919106027271
Material Nr. (12NC)	919106027271
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

# SlimLine TCS020

## Dimensional drawing

Dimensões em mm:

### Sobrepor (TCS 020)

