



Elegance TBS930

TBS930 2xTL5-14W/840 EB C5

2, TL5, 14 W, 840 neutral white, Electronic, High-gloss optic double parabolic

With their advanced design and compact size, Elegance luminaires are suitable for use in a wide variety of commercial lighting projects and offices, providing a contemporary and harmonious look. Available in recessed or surface-mounted versions and with two optical system options (C5 and CD), the TBS/SCT 930 luminaires add a touch of sophistication wherever they are installed. They were designed to be used with TL5 lamps of 14, 25, 28, 50 and 54 W - the most advanced technology in fluorescent lighting - which enable high levels of performance and therefore ensure exceptional energy savings.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	High-gloss optic double parabolic
Operating and Electrical	
Power Consumption	14 W

Product Data	
Order product name	TBS930 2xTL5-14W/840 EB C5
Full product name	TBS930 2xTL5-14W/840 EB C5
Full product code	919106027461
Order code	919106027461
Material Nr. (12NC)	919106027461
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400813499
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400813499

Elegance TBS930

Dimensional drawing

