



Elegance TCS930

TCS930 2xTL5-54W/840 EB CD

2, TL5, 54 W, 840 neutral white, Electronic, High-gloss optic decorative

With their advanced design and compact size, Elegance luminaires are suitable for use in a wide variety of commercial lighting projects and offices, providing a contemporary and harmonious look. Available in recessed or surface-mounted versions and with two optical system options (C5 and CD), the TBS/SCT 930 luminaires add a touch of sophistication wherever they are installed. They were designed to be used with TL5 lamps of 14, 25, 28, 50 and 54 W - the most advanced technology in fluorescent lighting - which enable high levels of performance and therefore ensure exceptional energy savings.

Product data

| General Information | |
|--------------------------|-----------------------------|
| Lamp family code | TL5 [TL5] |
| Gear | EB [Electronic] |
| Light Technical | |
| Number of light sources | 2 |
| Light source color | 840 neutral white |
| Optic type | High-gloss optic decorative |
| Operating and Electrical | |
| Power Consumption | 54 W |

| Product Data | |
|---------------------------------|----------------------------|
| Order product name | TCS930 2xTL5-54W/840 EB CD |
| Full product name | TCS930 2xTL5-54W/840 EB CD |
| Full product code | 919106027571 |
| Order code | 919106027571 |
| Material Nr. (12NC) | 919106027571 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Elegance TCS930

Dimensional drawing

Dimensões em mm:

