



SlimLine TBS020

TBS020 2xTL5-28W/840 EB R-H

2, TL5, 28 W, 840 neutral white, Electronic, Reflector high reflectance

SlimLine luminaires are compact and versatile for better distribution of light in the environment. Their slim design offers lots of advantages to designers and installers, with better adaptation to ceilings. Available in recessed (TBS020) and surface-mounted (TCS020) models with a choice of four optical systems. Ideal for 16 and 32 W TL-D tubular fluorescent lamps.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	Reflector high reflectance
Optical cover type	-
Operating and Electrical	
Power Consumption	28 W

Product Data	
Order product name	TBS020 2xTL5-28W/840 EB R-H
Full product name	TBS020 2xTL5-28W/840 EB R-H
Full product code	919106027709
Order code	919106027709
Material Nr. (12NC)	919106027709
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

SlimLine TBS020

Dimensional drawing

Dimensões em mm:

Embutir (TBS 020)

