



# TPS020

## TPS020 2XTL5-54W/840 EB R-H 5

2, TL5, 54 W, 840 neutral white, Electronic, Reflector high reflectance

The TPS020 luminaire has a high-reflectance, high-gloss aluminum reflector. This guarantees high performance, making this system the best lighting solution for retail applications. It also features excellent light distribution, elegance, and advanced technology. This surface-mounted luminaire consists of two TL5 lamps of 50 or 54 W and can be used to replace systems with luminaires for 110 W HO lamps. The high-performance electronic ballast ensures a longer lamp life and is internally mounted in the luminaire, preventing any risk of the wiring being disconnected accidentally during installation.

### Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	Reflector high reflectance
Operating and Electrical	
Power Consumption	54 W

Product Data	
Order product name	TPS020 2XTL5-54W/840 EB R-H 5
Full product name	TPS020 2XTL5-54W/840 EB R-H 5
Full product code	919106027829
Order code	919106027829
Material Nr. (12NC)	919106027829
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## TPS020

### Dimensional drawing

Dimensões em mm:

