



EcoBATTEN

TMS941 2xTL5-25W/840 EB WR-H

2, TL5, 25 W, 840 neutral white, Electronic, Wide beam high reflectance

EcoBATTEN is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25, 28, 50 or 54 W TL5 fluorescent tube lamps and can be used at heights of between 2.5 and 12 m. Available in five versions with high performance.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	EB [Electronic]
Light Technical	
Number of light sources	2
Light source color	840 neutral white
Optic type	Wide beam high reflectance
Operating and Electrical	
Power Consumption	25 W

Product Data	
Order product name	TMS941 2xTL5-25W/840 EB WR-H
Full product name	TMS941 2xTL5-25W/840 EB WR-H
Full product code	919106027922
Order code	919106027922
Material Nr. (12NC)	919106027922
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	7894400817848
Numerator - Packs per outer box	1
EAN/UPC - Case	7894400817848

Dimensional drawing

Dimensões em mm:

